

# Quick coupling plug KS2-M5-I

Part number: 531660

FESTO



## Data sheet

| Feature                                       | Value                                     |
|-----------------------------------------------|-------------------------------------------|
| Nominal size                                  | 2.7 mm                                    |
| Short type code                               | KS2                                       |
| Operating pressure complete temperature range | -0.95 bar ... 12 bar                      |
| Standard nominal flow rate                    | 135 l/min                                 |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium            | Lubricated operation possible             |
| Corrosion resistance class CRC                | 1 - Low corrosion stress                  |
| Ambient temperature                           | -10 °C ... 80 °C                          |
| Nominal torque                                | 0.85 Nm                                   |
| Tolerance for nominal tightening torque       | ± 15%                                     |
| Product weight                                | 5 g                                       |
| Pneumatic connection, port 1                  | Female thread M5                          |
| Note on materials                             | RoHS-compliant                            |