


Product information

97 52 65

Four-Mandrel Crimping Pliers for turned contacts




- Fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- Locator for positioning the contacts
- With table for calculating the settings
- Pliers in a plastic case with foam insert
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Special quality chrome vanadium electric steel, oil-hardened

General

| | |
|-----------------|----------------------------|
| Article No. | 97 52 65 |
| EAN | 4003773045236 |
| Pliers | chrome-plated |
| Head | chrome-plated |
| Handles | with multi-component grips |
| Weight | 676 g |
| Dimensions | 230 x 79 x 42 mm |
| REACH compliant | contains SVHC |
| RoHS compliant | not applicable |

Technical details



| | |
|--------------------------------|---|
| Application | turned contacts (Harting; Ilme; Phoenix; Amphenol; Walther; HTS; Contact; Weidmüller) |
| Capacity in square millimetres | 0.14 — 6 mm ² |
| AWG | 26 — 10 |
| Number of crimping positions | 1 |
| Max. contact diameter | 7.5 mm |

technical change and errors excepted