

ADG.2A ADG.2S ADG.2E

Luchtslijpmachine

EUROBOOR

FOR PROFESSIONALS BY PROFESSIONALS

Technische data

	Metrisch	Imperisch
As stiftrees Ø	6 mm	1/4"
Luchtinlaat	Ø 6,35 mm	1/4"
Luchtslang	Ø 9,525 mm	3/8"
Connector type	Euro, Orion, ISO B	
Gem. luchtverbruik		
	ADG.2A	0,113 m³/min - 4 SCFM
	ADG.2S	0,142 m³/min - 5 SCFM
	ADG.2E	0,142 m³/min - 5 SCFM
Werkdruk	6,3 bar	90 PSI
Toerental (onbelast)		
	ADG.2A	Max. 20.000 tpm
	ADG.2S	Max. 20.000 tpm
	ADG.2E	Max. 22.000 tpm
Gewicht	ADG.2A 0,53 kg	1,2 lbs
	ADG.2S 0,67 kg	1,5 lbs
	ADG.2E 1,31 kg	2,89 lbs
Lengte	ADG.2A 193 mm	7 5/8"
	ADG.2S 193 mm	7 5/8"
	ADG.2E 338 mm	13 5/16"
Hoogte	70 mm	2 3/4"

Kenmerken



Regelbaar
toerental



Werkdruk:
min. 6,3 bar
(90 PSI)



ADG.2A



ADG.2S



ADG.2E

Euroboor stelt alles in het werk om te voldoen aan kwaliteits- en integriteitseisen. Daarom zijn wij als organisatie trots op de erkenning van enkele toonaangevende instanties wereldwijd:



www.euroboor.com