

120° conical countersink, HSS, triple cutter

for universal use up to 1000 N/mm²

ORION[®]

Application:

For producing 120° counterbores up to 1000 N/mm².

Execution:

- profile-ground triple-edge countersink with radial relief

Advantage:

- radial relief ensures optimum chip breaking



Art. no.	11502 312
Brand	ORION
Manufacturer Part Number	11502312
Countersink angle	120 Degree
Cutting material	HSS
Surface	Uncoated
Number of cutting edges	3 PCS
Tool holding device	HA parallel shank
Spot-facer diameter	12.5 mm
Tip diameter	2.8 mm
Shank diameter	8 mm
Length	54 mm
f steel 700	0.13 mm/r
Gross Weight	0.025 kg
Product Group	1EH

EAN

4053625033195