

# HUBER+SUHNER® DATA SHEET

## Coaxial PCB Connector: 81\_MCX-50-0-6/111\_N



### Description

Straight PCB plug

Interface standards  
IEC 60169-36\_CECC 22220



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 6 GHz

#### Mechanical Data

Board mounting type through holes  
Weight 0.0009 kg

#### Environmental Data

Operating Temperature -55 °C to 155 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

Centre contact	Brass
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

##### Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)

#### Related Documents

Outline drawing	DOU-00013049
Catalogue drawing	DCA-00013051

#### Ordering Information

Bulk 100 pcs package	81_MCX-50-0-6/111_NH
Single package	81_MCX-50-0-6/111_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**