

Blanking plug CQC-18H

FESTO

Part number: 177714



Data sheet

Feature	Value
Maritime classification	See certificate
Type code	CQC
Mounting position	Any
Pack size	1
Design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 7 bar
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	-25 °C ... 70 °C
Product weight	8 g
Pneumatic connection 1	Push-in sleeve CQ-18
Pneumatic connection 2	Push-in sleeve CQ-18
Note on materials	RoHS-compliant Contains paint-wetting impairment substances
Blanking plug material	POM