

Slides DZ 5417, width 17.5 mm, up to 100 kg, Over-Extension

Material:

Slide elements: Cold-rolled, bright zinc-plated steel.

Ball retainers: Cold rolled steel, zinc-plated.

Balls: Hardened steel.


Telescopic precision ball bearing slides for applications in the industrial and electronics sector.

- Hold-in in the closed position.
- Service life 10,000 cycles.
- Temperature range: -20°C to +70°C.



Accuride

Ordering Details: e.g.: Product No. 649 049 30, Slides DZ 5417



Product No. per Pair	Slide Length mm	Travel +/-3,2 mm	A mm	B mm	C mm	D mm	E mm	F mm	G mm	H mm	Load Rating per Pair kg	Weight per Pair kg
649 049 30	300	340	-	-	224	256	-	-	-	256	90	1,64
649 049 35	350	389	-	-	224	256	-	-	-	256	90	1,93
649 049 40	400	438	160	192	320	352	128	160	-	352	92	2,22
649 049 45	450	487	160	192	320	352	128	160	320	352	95	2,53
649 049 50	500	537	192	224	416	448	160	192	-	416	100	2,81
649 049 55	550	586	224	-	448	480	160	192	-	448	100	3,12
649 049 60	600	635	256	288	480	512	192	224	480	512	94	3,41
649 049 65	650	684	288	320	544	576	192	256	-	544	92	3,68
649 049 70	700	733	288	416	576	608	256	288	576	608	90	4,00

Note

Recommended fastening: M4 screw.

Use all mounting positions to achieve the max. load rating.



Hinges
Page 753