

Electronic dial gauge

ID-C with low gauging force

Mitutoyo

Application:

for measuring lengths and differences in length, e.g. concentricity, flatness, position measurements.

Version:

- Preset function
- ON/OFF
- ABSOLUTE system for reliable measurement
- LCD digit size 11 mm
- LOCK function (key lock)
- Digimatic



| | |
|---|--|
| Art. no. | 32019 285 |
| Length measuring range | 12.7 mm |
| Digit increment | 0.01 mm |
| Min./max. measurement force | 0.2-0.5 N |
| Error limit | 0.02 mm |
| Repeat accuracy | 0.01 mm |
| Data transmission type | DIGIMATIC |
| IP protection class | IP 42 |
| Functions | Absolute function, Preset function, On/Off, Reversal of counting direction |
| Absolute function | Yes |
| Automatic switch-off | No |
| Dynamic measurement | No |
| Preset function | Yes |
| Shank diameter | 8 mm |
| Tolerance value entry | No |
| Manual tolerance markers | No |
| Calibration Group | CE |
| Colour reading classification | No |
| Number of rechargeable batteries/batteries | 1 PCS |
| Battery designation | 1,5 V SR44 |
| Rotating housing | Yes |
| Combined indicator for figure/scale reading | No |
| Reversible counting direction | Yes |
| Digit height | 11 mm |
| Design | Metric |
| Display | Digital |
| Calibration Group Description | Dial gauge |
| WEEE (taking back waste electrical and electronic equipment) | 5 |

EAN-Code

4946368586656