

ARCA 304015

FIBOX
Enclosing innovations



Sample image

Order symbol: ARCA 304015

Product nbr: 8120022

Description: Cabinet, PC


Remarks: Grey cover, 2-point locking, hinges on the short side

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate, 3mm double bit lock(s) with key, 5 versions with swinghandle 2-point locking system, Door guide included.

EAN: 6418074079336

El. number:

- Finland: 3423119
- Denmark: 8212091207
- Sweden: 2500111



Dimensions:	Height	Width	Depth
mm:	300	400	150
inch:	11.81	15.75	6.22

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120
Temperature °C (continuous):	-40 ... 80
Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175

Accessories:

DRS ARCA 304015	DIN rail frame set (385 x 285 x 35)
SBK ARCA 30	Support bar kit (235 x 40 x 30)
DSP ARCA HRS	Door stopper ARCA, horizontal, right, small
DSP ARCA HLS	Door stopper ARCA, horizontal, left, small
SBK ARCA 40	Support bar kit (340 x 40 x 30)
IDS ARCA 3040	Inner door set (285 x 385 x 35)
RCS ARCA 3040	Rain canopy set for size 3040 (20 x 400 x 30)
PMK ARCA 40	PoleMounting kit, for pole \varnothing 100-300mm (385 x 285 x 35)
MPP ARCA 3040	Mounting plate perforated (350x250x2 mm - 26x11 mm) (250 x 350 x 2)
MPMP ARCA 4030	Mounting plate multiperforated (350x250x2 mm - \varnothing 3.6 mm) (350 x 250 x 2)
MPS ARCA 4030	Mounting plate (350x250x2 mm) (350 x 250 x 2)
MPX ARCA 4030	Mounting plate (350x250 mm) (350 x 250 x 5)

Rating:

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK10;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	NEMA 1, 4, 4X, 12 and 13

Certificates:

Certificate FI 40467