



## NHS-19.1-0-2.5M

SHRINK TUBE WITHOUT ADHESIVE, 2:1, ID=19.1mm BLACK, L=2.5m, THIN-W

Standard heat shrink tubing with shrink ratio 2:1

### Applications:

Electrical insulation, strain relief, bundling, mechanical protection, colour coding of wires, cables, tubes and electronic components.

Blister pack.

Material: Polyolefin

Colour: Black

Temperature range: Max. +125° C (+257° F)

Lowest shrink temperature: +90° C (+194° F)

Wall thickness: Thin wall

Shrink ratio: 2:1

Self-extinguishing: VW-1



## Product Properties:

Model	Thin-walled
Type	Heat-shrink
Shrink rate	2:1
With inner glue	No
Colour	Black
Material	Polyolefin (PO-X)

Halogen free	No
Packaging	Assortment
Operating temperature	-55-125 °C

### **Dimensions:**

Unit	pck
Wall thickness after shrinking	0,8 mm
Length	2,5 m
Inner diameter before heat-shrink	18,7 mm
Inner diameter after heat-shrink	9,35 mm
MOQ	1 .

### **Approvals:**

Approved according to UR	Yes
Approved according to CSA	Yes
UL approval	No

### **Compliance:**

RoHS	RoHS 3 (2015/863)
Reach	No SVHC (219 Subs. Jul 2021)
SCIP	Not Applicable

### **Other information:**

ETIM-Class	EC000217 - Shrink tubing
ETIM-Release	7.0
Product Group	Retailer Concepts & Assortments
Search Description	KRYMPSLANG UTAN LIM, 2:1, ID=19.1MM, SVART
Alternative SKU	NHS-19.1-0-2.5M

### **Logistic information:**

Barcode	733117614388
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales., Non Stock Item, can be on stock but is not a regular stock item.
Packaging	Assortment
Stock code	NHS-19.1-0-2.5M
Taric code	39173200
Unit	pck
MOQ	1 .