

J.19 J - 3/8" metric 12-point sockets**Description:**

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.

A [mm]:	19
d [mm]:	22,7
d1 [mm]:	26,0
L [mm]:	33
L1 [mm]:	14,0
12-Point [mm]:	12
[g]:	62

