

NSYTBS19128

ABS box IP66 IK07 RAL7035
Int.H175W105D80 Ext.H192W121D87 Opaque
cover H20



Main

Range	Thalassa
Product name	Thalassa TBS
Device application	Multi-purpose
Category	Industrial box
Height	7.56 in (192 mm)
Maximum Width	4.76 in (121 mm)
Depth	3.43 in (87 mm)
Internal height	6.89 in (175 mm)
Internal width	4.13 in (105 mm)
Internal depth	3.15 in (80 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 2
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	ABS (acrylonitrile butadiene-styrene)
Color	Grey (RAL 7035)
Standards	IEC 62208
Product certifications	TÜV
Electrical insulation class	Class II
IP degree of protection	IP66 NEMA 4.4X
IK degree of protection	IK07 conforming to IEC 62262
Glow wire resistance	1202 °F (650 °C) IEC 60695-2-11
Ambient air temperature for storage	5...104 °F (-15...40 °C)
Operating temperature	-13...140 °F (-25...60 °C)
Net Weight	0.74 lb(US) (0.335 kg)

Ordering and shipping details

Category	80033 - ENCLOSURE SYSTEMS POLYESTER
Discount Schedule	ES1
GTIN	03606480165283
Nbr. of units in pkg.	2
Package weight(Lbs)	0.74 lb(US) (0.34 kg)
Returnability	No
Country of origin	HU

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Package 1 Height	7.87 in (200.000 mm)
Package 1 width	6.30 in (160.000 mm)
Package 1 Length	10.24 in (260.000 mm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------