

## Precision scales 572

robust metal housing, bestseller for many applications

**KERN**

### Application:

Versatile applications; suitable for use e.g. as laboratory scales, counting scales or check-weigher scales.

### Execution:

- Robust metal housing
- LCD display with 14 mm digit size
- Automatic reference optimisation
- Mechanical overload protection
- Options: Battery operation
- Integrated KERN Universal Port (KUP): Connection of external KUP interface adapters, such as RS-232, USB, Bluetooth, Wi-Fi or Ethernet. (Adapter not included in scope of delivery.) This means that interfaces may easily be retrofitted without the need to open the scale housing and without complicated installation
- KERN Communication Protocol (KCP): The KCP allows for placing queries and remote control of the scale via external control units or computers

### Advantage:

- User-programmable weighing unit (thread length g/m, paper weight g/m<sup>2</sup>)
- 572 model series scales can be integrated into the KERN Easy Touch system.

### Delivery:

Mains adapter



<b>Art. no.</b>	<b>44615 010</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	572-33
<b>Type description</b>	572-33
<b>Max. weight measuring range</b>	1610 g
<b>Digit increment, weight</b>	0.01 g
<b>Plate diameter</b>	150 mm
<b>With unit counting</b>	Yes
<b>Min. item weight</b>	0.03 g
<b>Reproducibility</b>	0.01 g
<b>Linearity</b>	0.03 g
<b>Data transmission type</b>	RS232
<b>Housing dimensions (LxWxH)</b>	310 x 180 x 90 mm
<b>Gross Weight</b>	4.000 kg
<b>Product Group</b>	447

### EAN

4045761014169