



Sample photo

Order symbol: PCT 162409
Product nbr: 7022811
Description: Enclosure, PC
Remarks: Clear transparent cover

EAN: 6418074058676
EI. number:
 Finland: 3435414
 Electric No. 8212002937
 Denmark:
 Electric No. Sweden: 7022811

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	244	164	90	Ingress Protection (EN 60529): IP66/IP67
inch:	9.6	6.5	3.5	Impact Resistance (EN 62262): IK07/IK08
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			UV resistance: UL 508
Cover screws material:	Stainless steel			Flammability Rating: UL 746C 5V
Cover colour:	Clear transparent			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:	Polyurethane			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:				Certificates:
Temperature °C (short term):	-40 ... 120 °C			SGS Fimko
Temperature °C (continuous):	-40 ... 80 °C			Gost R
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			

EURONORD PC/ABS 244x164x90-120

