


13100-146 PSU 19" FOR COMPACTPCI, DC/DC, 6 U, 8 HP



**KEY FEATURES**

Connector P47 and CompactPCI signalling

4 output voltages

Redundant operation with Current Share Bus (CSB), hot-swap

**PRODUCT ATTRIBUTES**

Product Type: Power Supply

Type: 19" DC/DC Converter

Works With: CompactPCI and VME64x

Input Voltage DC: 36 – 72 V

Power: 500 W

Number of Output Voltages: 4

Voltage 1: 5 V

Current 1: 50 A

Voltage 2: 3.3 V

Current 2: 60 A

Voltage 3: 12 V

Current 3: 12 A

Voltage 4: -12 V

Current 4: 4 A

Rack Height: 6 U

Rack Width: 8 HP

## ADDITIONAL PRODUCT DETAILS

---

Pluggable 19" Power Supply with P47 connector, for CompactPCI applications.

Output data at Ta=-10...-55°C with forced air cooling of 2-m/s.

## CERTIFICATIONS

---





### North America

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.