

Quick coupling plug KS3-1/8-I

Part number: 531668

FESTO



Data sheet

Feature	Value
Nominal size	4.95 mm
Short type code	KS3
Operating pressure complete temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	558 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Nominal torque	5 Nm
Tolerance for nominal tightening torque	± 15%
Product weight	16 g
Pneumatic connection, port 1	Female thread G1/8
Note on materials	RoHS-compliant