



Y-splitter

ZDO2H040VAS0000-00STGH050VAS



| Application                       |      |                                                                   |
|-----------------------------------|------|-------------------------------------------------------------------|
| Special feature                   |      | Free from silicone; Gold-plated contacts                          |
| Free from silicone                |      | yes                                                               |
| Electrical data                   |      |                                                                   |
| Operating voltage                 | [V]  | < 60 AC/DC                                                        |
| Protection class                  |      | II                                                                |
| Max. current load per module/slot | [A]  | 4                                                                 |
| Max. current load total           | [A]  | 4                                                                 |
| Operating conditions              |      |                                                                   |
| Ambient temperature               | [°C] | -25...100                                                         |
| Protection                        |      | IP 65; IP 67; IP 68; IP 69K                                       |
| Mechanical data                   |      |                                                                   |
| Weight                            | [g]  | 34.2                                                              |
| Materials                         |      | Housing: PA Halogen-free; Sealing: EPDM                           |
| Material nut                      |      | stainless steel (1.4404 / 316L) / stainless steel (1.4404 / 316L) |
| Remarks                           |      |                                                                   |
| Pack quantity                     |      | 1 pcs.                                                            |


Electrical connection - plug

Connector: 1 x M12; Moulded body: PA, Halogen-free; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.6...1.2 Nm




## Y-splitter

ZDO2H040VAS0000-00STGH050VAS



### Connection



connection to IEC 61076-2-101

### Electrical connection - socket

Connector: 2 x M12; Moulded body: PA, Halogen-free; Locking: stainless steel (1.4404 / 316L); Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm

