

Angular milling cutter HSSE Co 5


ORION[®]

Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

Execution:

- Straight-grooved
- Finely toothed
- Straight shank according to DIN 1835 B.
- For cutting on periphery and end face



Art. no.	15814 155
Brand	ORION
Manufacturer Part Number	15814155
Cutting material	HSSE Co5
Type	N
Number of cutting edges	12 PCS
Chamfer angle	60 Degree
Tool holding device	HB parallel shank
Cutting edge diameter	32 mm
Width of cutting edge	12.5 mm
Immersion depth	23 mm
Length	71 mm
Shank diameter	16 mm
Form	C
fz steel 700	0.08 mm
Gross Weight	0.200 kg
Product Group	106

EAN

4039247098149