

INDIGA round files

Type 9030

LAPPORT
SCHLEIFTECHNIK

Application:

For sharpening and reworking tools for wood, metal and plastic processing, e.g. scrapers, machine and plane knives, steels, reamers and gauges as well as measuring instruments.

Execution:

- Best used with thin-bodied oil, petroleum or water
- Machined and wetted on all sides after burning

Advantage:

- High endurance and grinding force



Art. no.	69344 320
Brand	LAPPORT
Manufacturer Part Number	100426
Binding	Ceramically bound
Surface structure	Fine
Grid size	400
Form	Round
Length	100 mm
Width	10 mm
Number of pieces per packet	6 PCS
Diameter	10 mm
Material of abrasive medium	Corundum
Diameter x length	10 x 100 mm
Suitable for finishing	2 - suitable
Suitable for main machining	2 - suitable
Suitable for surface inspection	3 - less suitable
Suitable for surface care	2 - suitable
Suitable for material rubber	3 - less suitable
Suitable for material cast iron	2 - suitable
Suitable for material HSS	3 - less suitable
Suitable for material carbide	3 - less suitable
Suitable for material ceramic	3 - less suitable
Suitable for material plastics	3 - less suitable
Suitable for material non-ferrous metals	3 - less suitable
Suitable for material steel (hardened)	2 - suitable
Suitable for material steel (unhardened)	1 - very suitable
Suitable for material tool steel	2 - suitable
ISO	525
Length x width	100 x 10 mm
Type description	Corundum
Gross Weight	0.021 kg
Product Group	6HL