

## ATTIX 30-01 wet and dry vacuum cleaner



### Application:

Multi-purpose vacuum cleaner for industry and skilled trades.

### Delivery:

suction hose D32 x 3.5 m, aluminium extension pipes D36 2 x 500 mm, floor nozzle, joint nozzle, PET filter element Ø 185 x 140 mm, filter bag

<b>Art. no.</b>	<b>75521 042</b>
<b>Brand</b>	NILFISK
<b>Manufacturer Part Number</b>	107413590
<b>Model</b>	ATTIX 30-01
<b>Power input</b>	1500 W
<b>Max. air delivery volume</b>	3700 l/min
<b>Underpressure</b>	250 mbar
<b>Bin capacity</b>	30 l
<b>Sound-pressure level</b>	59 dB
<b>Weight</b>	10 kg
<b>Cable length</b>	7.5 m
<b>With device connector</b>	No
<b>With antistatic system</b>	No
<b>With automatic shut off</b>	No
<b>With accessory tray</b>	Yes
<b>With soft start</b>	No
<b>Length x width x height</b>	450 x 380 x 595 mm
<b>With speed control</b>	No
<b>Nominal voltage</b>	230 V
<b>Gross Weight</b>	14.000 kg
<b>Product Group</b>	7AJ



### EAN

5711145265142