

EAN : 542503 853152 7

SKU : SXAE00125

- Start deeply 12V battery vehicle engine
- Max peak amp : 700 Amp
- Polarity inversion and short circuit protection
- 2x USB output : charge all your electronic devices (phone, tablet, MP3,..)
- Built-in light
- LCD charge level indicator
- Nylon carrying case



SPECIFICATIONS

Input	Voltage	USB 5.0V DC 2.0A				
Output	Nominal Voltage	For 12V Vehicle (14.8V)				
	Start Amp	350A				
	Max Peak Amp	700A				
	Power	Safe Smart Cable				
	USB	1X USB 5V 2,1A / 1X USB 5V 1.0A				
Battery	Type	Lithium ion battery (Pouch cell)				
	Capacity	26,64Wh 7.200mAh				
Interface	Charge level	LCD Charge indicator				
	MMI	On / Off Selector - Power buton				
Others	Buid in Light	YES				
	Certification	CE				
Start engine	Displacement	Gasoline up to 4.0L		Diesel up to 1.5L		
SKU	EAN code	542503 853152 7				
	Length	147mm	Width	71mm	Height	231mm
	Gross weight	855gr	Net weight	680gr		
CRATE	EAN code	2 542503 853152 1				
	Length	159mm	Width	159mm	Height	267mm
	Gross weight	2,10kg	Net weight	1,85kg		
	Qty of SKUs per crate	2				
PALLET	EAN code	4 542503 853152 5				
	Length	120cm	Width	80cm	Height	125cm
	Gross weight	256kg	Net weight	236kg		
	Crates per layer	16	Qty of layers	7	Crates per pallet	112
	Qty SKUs per pallet	224				
	type of pallet	composite board pallet				