

29754

Aluminium Telescopic  
handle, 1575 - 2780 mm,  
Ø32 mm, Red



This telescopic handle can be easily adjusted to the required length, making it ideal for cleaning walls and canopies. Its ergonomic design and comfortable grip improve user comfort. Can be used with any product in the Vikan range. Do not use with acid or chlorine.

# Technical Data

Item Number	29754
Material	Anodised Aluminium Polypropylene
Complies with (EC) 1935/2004 on food contact materials <sup>1</sup>	No
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of phthalates and bisphenol A	No
Is Halal and Kosher compliant	Yes
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	500 Pcs.
Quantity Per Layer (Pallet)	25 Pcs.
Box Length	1650 mm
Box Width	140 mm
Box Height	85 mm
Product Diameter	32 mm
Length/Depth	1575 mm
Width	32 mm
Height	32 mm
Max. Length	2780 mm
Net Weight	0,95 kg
Weight cardboard	0,06 kg
Tare total	0,06 kg
Gross Weight	1,01 kg
Cubik metre	0,001613 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature <sup>3</sup>	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	8 pH
GTIN-13 Number	5705020297540
GTIN-14 Number (Box quantity)	15705020297547
Customs Tariff No.	76082020
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.