



E33212



Process adapter hygienic pipe fitting

ADAPT IFM-DIN11851 DN40/1.5"



1 Aseptoflex Vario
2 sealing area

EC 1935/2004

Application		
Pressure rating	[bar]	40
Tests / approvals		
Pressure Equipment Directive		A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions		The compatibility between medium and product material has to be checked in all applications.
Mechanical data		
Weight	[g]	197
Materials		stainless steel (1.4435 / 316L)
Sensor connection		G 1 external thread Aseptoflex Vario
Process connection		hygienic pipe fitting DN40 (1,5") DIN 11851
Surface characteristics Ra/Rz of the wetted parts		0.4 / 4
Sealing		Gasket
Hygienic equipment class to DIN 11866		H4
Accessories		
Accessories (supplied)		O-rings: 1 x 24 x 2 (EPDM), FDA compliant
Accessories (optional)		O-ring: 1 x 24 x 2 (FKM), FDA compliant, E30123 sealing ring: 1 x PEEK, FDA compliant, E30124
Remarks		
Pack quantity		1 pcs.