

Fixed ball-type tap wrench

For mounting screw taps and hand reamers

ORION[®]

Application:

For mounting screw taps and reamers with square.

Version:

- Steel tool holder with screw-off arm and 4 square holes to DIN 10

Advantage:

- High-quality steel with very good wear characteristics and chromium-plated extensions for high corrosion resistance
- User-friendly handling and short retooling times
- Excellent value for money



Art. no.	13545 005
Tap wrench size	0
Square size	2.1 mm/2.7 mm/3 mm/3.4 mm
Min./max. thread-cutting area, metric	1-4 mm
Min./max. thread-cutting area, imperial	1/16-5/32 in
Length	170 mm

EAN-Code

4039247076550