

# AC-DC Switching Adapter

## 27 W, Euro plug



### FEATURES:

With over voltage, over current and over power protection

### SPECIFICATION:

Output voltage	12 VDC
Power	27 W
Connection, primary side	Euro plug
Connection, secondary side	2.5 x 5.5 x 11 mm Barrel plug
Input voltage	100...240 VAC
MTBF	50 000 Hours min
Output current	0...2.25 A
Cable length	1.5 m
Dimensions L x W x H	87.5 x 51 x 77.3 mm
Input frequency	50...60 Hz
No load power consumption	< 0.3 W
Line regulation	0.5 %
Operating temperature max.	35 °C
Operating temperature min.	0 °C
Short-circuit-proof	Yes
Weight	200 g
Appliance	Class II
Efficiency	Efficiency level V



### Art. Nr.

**RND 320-00032**

For more information and technical drawings, please contact us at [info@distrelec.com](mailto:info@distrelec.com).

