

H1,5/14 R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

| | |
|------------|---------------------------------------------------------------------------------------|
| Type | H1,5/14 R |
| Order No. | 0463100000 |
| Version | Wire end ferrule, 1.5 mm ² , 8 mm, Colour code: Weidmüller, Red (RAL 3020) |
| GTIN (EAN) | 4008190065089 |
| Qty. | 500 pc(s). |

H1,5/14 R

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|--------|-------|------------|---------|
| Length | 14 mm | Net weight | 0.108 g |
|--------|-------|------------|---------|

Product data

| | | | |
|-------------------------------|---------------------|-----------------------------------------|---------|
| Conductor cross-section | 1.5 mm ² | Wire connection cross section AWG, max. | AWG 16 |
| Contact surface length (L2) | 8 mm | Contact surface diameter (D1) | 1.7 mm |
| Collar diameter (D2) | 3.5 mm | Metal sleeve thickness (S1) | 0.15 mm |
| Plastic collar thickness (S2) | 0.25 mm | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000005 | UNSPSC | 31-16-31-02 |
| eClass 5.1 | 27-40-02-01 | eClass 6.2 | 27-40-02-01 |
| eClass 7.1 | 27-40-02-01 | | |

Approvals

Approvals



ROHS Conform