

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 970
Brand	AMF
Manufacturer Part Number	81109
DIN	787
Thread dimension	M24
Groove width	28 mm
Length excluding head	160 mm
Outer diameter	27.7 mm
Thread length	110 mm
Length of head	44 mm
Head height	18 mm
Gross Weight	1.095 kg
Product Group	260

EAN

4020772081102