

**Clamping yoke  
KLBUE CO 5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals.

These are available in different versions.

**General ordering data**

Type	KLBUE CO 5
Order No.	<a href="#">1755081001</a>
Version	Clamping yoke, Clamping yoke, Steel
GTIN (EAN)	4032248064472
Qty.	10 pc(s).

**Data sheet**

**Clamping yoke  
KLBUE CO 5**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	42.7 mm	Height	35.5 mm
Depth	64.5 mm	Net weight	78.7 g

**Additional technical data**

Explosion-tested version	No	Installation advice	Busbar
Version	For a shield connection		

**Wire clamp for cable diameter**

Cable diameter, min.	20 mm	Cable diameter, max.	37 mm
----------------------	-------	----------------------	-------

**Material data**

Material	Steel
----------	-------

**System specifications**

Product family	Clamping yoke
----------------	---------------

**Classifications**

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 6.2	27-14-11-90
eClass 7.1	27-14-11-50	eClass 8.1	27141150
eClass 9.0	27141150		

**Approvals**

Approvals



ROHS	Conform
------	---------