

# LED Tubes

- Full Glass Design with Protective Shatterproof Coating
- Includes LED Starter
- 4000K and 6500K Alternatives
- 4ft, 5ft and 6ft Alternatives

# Strip Tubes

- Replacements for 30w and 50w Incandescent
- 2700K Output
- 221mm and 284mm alternatives
- Opal finish

- Easy Replacement
- Flicker Free Design
- Even Light Distribution
- True Retro Fit
- Automated Production
- IC Drivers
- Instant Light

G13



S15



## 4FT AND 5FT TUBES – 36W & 58W REPLACEMENT – 30,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S8912	Box	18w	G13	x	30000 hrs	1800lm	4000K	4ft (1.2mtr)	n/a	12
S8913	Box	22w	G13	x	30000 hrs	2260lm	4000K	5ft (1.5mtr)	n/a	12
S8914	Box	18w	G13	x	30000 hrs	1800lm	6500K	4ft (1.2mtr)	n/a	12
S8915	Box	22w	G13	x	30000 hrs	2260lm	6500K	5ft (1.5mtr)	n/a	12

## STRIP TUBE – 30W REPLACEMENT – 15,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9217	Box	3.5w	S15	x	15000 hrs	350lm	2700K	25x221	12	72

## STRIP TUBE – 50W REPLACEMENT – 15,000 HOURS

Part Number	Pack	Watt.	Cap	Dimmable	Life	Lumen	Colour Temp.	Lamp Dims.	Inner Qty.	Outer Qty.
S9218	Box	5.5w	S15	x	15000 hrs	550lm	2700K	25x284	12	72