



Amp	Volt	Hz	IP Ident. colour + h	 Part No.
-----	------	----	-------------------------------	---

Plugs and sockets for extra-low voltages 2 pole up to 50 V

IEC/EN 60 309



16	24~	50/60	-	10 110
	42~	50/60	12	10 111
	42~	100/200	4	10 112
	42~	300	2	10 113
	42~	400	3	10 114
	42~	>400/500	11	10 115
	42 ...	-	10	10 116
32	24~	50/60	-	11 110
	42~	50/60	12	11 111
	42~	100/200	4	11 112
	42~	300	2	11 113
	42~	400	3	11 114
	42~	>400/500	11	11 115
	42 ...	-	10	11 116

wall socket outlets, external fixing means, 1 top cable entry

Ampère	b	c	d	e	f	l	n	Pg
16 A	54,5	5,2	81	70	72	28	119	21
32 A	54,5	5,2	81	70	72	28	119	21

10	003747
169	003754
	003761
	003778
	003785
	003792
	003808
	005819
10	121656
	005826
	005833
169	005840
	005857
	005864

16	24~	50/60	-	10 100
	42~	50/60	12	10 101
	42~	100/200	4	10 102
	42~	300	2	10 103
	42~	400	3	10 104
	42~	>400/500	11	10 105
	42 ...	-	10	10 106
32	24~	50/60	-	11 100
	42~	50/60	12	11 101
	42~	100/200	4	11 102
	42~	300	2	11 103
	42~	400	3	11 104
	42~	>400/500	11	11 105
	42 ...	-	10	11 106

wall socket outlets, external fixing means, cable entries: top: 1 x Pg 21, bottom: 2 x Pg 16

Ampère	b	c	d	e	f	l	n
16 A	80	6,2	93	90	93	60	125
32 A	80	6,2	93	90	93	60	125

10	003679
213	003686
	003693
	003709
	003716
	003723
	003730
	005741
10	005758
	005765
	005772
213	005789
	005796
	005802

16	24~	50/60	-	10 280
	42~	50/60	12	10 281
	42~	100/200	4	10 282
	42~	300	2	10 283
	42~	400	3	10 284
	42~	>400/500	11	10 285
	42 ...	-	10	10 286
32	24~	50/60	-	11 280
	42~	50/60	12	11 281
	42~	100/200	4	11 282
	42~	300	2	11 283
	42~	400	3	11 284
	42~	>400/500	11	11 285
	42 ...	-	10	11 286

plugs, flexible cable entry

Ampère	d	e	f	m	n	Op
16 A	135	59	55	99	22,5	8/21
32 A	135	59	55	99	22,5	8/21

10	004379
110	004386
	004393
	004409
	004416
	004423
	004430
	006441
10	006458
	006465
	006472
110	006489
	006496
	006502

16	24~	50/60	-	10 210
	42~	50/60	12	10 211
	42~	100/200	4	10 212
	42~	300	2	10 213
	42~	400	3	10 214
	42~	>400/500	11	10 215
	42 ...	-	10	10 216
32	24~	50/60	-	11 210
	42~	50/60	12	11 211
	42~	100/200	4	11 212
	42~	300	2	11 213
	42~	400	3	11 214
	42~	>400/500	11	11 215
	42 ...	-	10	11 216

plugs, gland entry Pg 16

Ampère	d	e	f	m	n	Pg
16 A	128	59	55	99	22,5	16
32 A	128	59	55	99	22,5	16

10	004089
108	004096
	004102
	004119
	004126
	004133
	004140
	006151
10	006168
	006175
	006182
108	006199
	006205
	006212