

Product information

97 52 36

KNIPEX PreciForce®
Crimping Pliers

- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened



General

| | |
|-----------------|----------------------------|
| Article No. | 97 52 36 |
| EAN | 4003773051893 |
| Pliers | burnished |
| Handles | with multi-component grips |
| Weight | 487 g |
| Dimensions | 220 x 63 x 23 mm |
| REACH compliant | contains SVHC |
| RoHS compliant | not applicable |

Technical details



| | |
|--------------------------------|--|
| Application | insulated terminals, plug connectors + butt connectors |
| Capacity in square millimetres | 0.5 — 6.0 mm ² |
| Number of crimping positions | 3 |
| AWG | 20 — 10 |

technical change and errors excepted



97 52 36