



MASTER Value Glass LED bulbs

MASTER VLE LEDBulb DT5.9-60W E27 927ST64CLG

Featuring a classic heritage design, these filament LED bulbs combine the familiar shapes of incandescent bulbs with the benefits of long-lasting LED technology. These MASTER Value Glass LED bulbs offer more energy savings than normal glass LED bulbs. At the same time, they also provide customers with good light experience, enhanced by excellent dimming performance (dimmable glass LED bulbs). MASTER Value Glass LED Bulbs deliver significant energy savings, using 30% less energy compared to normal LED bulbs and provide excellent quality of light. By offering a lifetime of 15,000 hours, these dimmable LED bulbs also reduce maintenance costs.

Product data

General information		Color Rendering Index (Nom)	
Cap-Base	E27 [E27]		90
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom) 70 %	
Nominal Lifetime (Nom)	15000 h	Operating and electrical	
Switching Cycle	20000X	Input Frequency	50 to 60 Hz
Flux measurement reference	Sphere	Power (Nom)	5.9 W
		Lamp Current (Nom)	40 mA
Light technical		Wattage Equivalent	60 W
Color Code	922-927 [CCT of 2200K-2700K]	Starting Time (Nom)	0.5 s
Luminous Flux (Nom)	806 lm	Warm Up Time to 60% Light (Nom)	0.5 s
Color Designation	Warm Glow(WG)	Power Factor (Nom)	0.6
Correlated Color Temperature (Nom)	2200 2700 K	Voltage (Nom)	220-240 V
Luminous Efficacy (rated) (Nom)	136.00 lm/W		
Color Consistency	<6		

MASTER Value Glass LED bulbs

Temperature

T-Case Maximum (Nom)	70 °C
----------------------	-------

Controls and dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and housing

Bulb Finish	Clear
-------------	-------

Bulb Shape	ST64
------------	------

Approval and application

Energy Efficiency Class	D
-------------------------	---

Energy Consumption kWh/1000 h	6 kWh
-------------------------------	-------

EPREL Registration Number	453250
---------------------------	--------

Product data

Full product code	871951432481700
-------------------	-----------------

Order product name	MASTER VLE LEDBulb DT5.9-60W E27 927ST64CLG
--------------------	---

EAN/UPC - Product	8719514324817
-------------------	---------------

Order code	929003010702
------------	--------------


Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	10
---------------------------------	----

Material Nr. (12NC)	929003010702
---------------------	--------------

Net Weight (Piece)	0.048 kg
--------------------	----------


Dimensional drawing




MASTER VLE LEDBulb DT5.9-60W E27 927ST64CLG

Product	D	C
MASTER VLE LEDBulb DT5.9-60W E27 927ST64CLG	64 mm	140 mm

Photometric data




LEDbulb MAS SLR 5,9W A60 E27 927 CL-POC



LEDbulb MAS SLR ST64 5,9W E27 927 CL-LDD

MASTER Value Glass LED bulbs

Photometric data




© Philips Lighting N.V. 2021

LEDbulb MAS SLR 5,9W ST64 E27 927 CL-GUL

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram

