

- 6101-0042 - HPS-502-G-Range D
- Pressure range - 25 to 75 mBar (10" to 30" H<sub>2</sub>O)
- Proof Pressure - 623 mBar (250" H<sub>2</sub>O)
- Pressure connection - Perpendicular ports
- Single pole normally open
- Diaphragm material - Urethane
- Operating Temperature +4°C to +65°C
- Electrical rating - 10/20mA 24V
- Mechanical life - 20,000,000 cycles



## Outline Dimensions

