

Product information

97 71 180

Crimping Pliers for wire ferrules




- Light and slim design
- Also as VDE version
- Easy crimping due to optimised transmission ratio
- For crimping wire ferrules according to DIN 46228 parts 1 + 4 from 0.25 to 16 mm²
- Crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened

General

Article No.	97 71 180
EAN	4003773040668
Head	polished
Handles	plastic coated
Weight	205 g
Dimensions	180 x 49 x 15 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details



Application	Wire ferrules
Capacity in square millimetres	0.25 — 16.0 mm ²
Number of crimping positions	9
AWG	24 — 6

technical change and errors excepted

