

Combination spanner (DIN 3113 B)

DIN 3113 B, jaw angle 15°, ring side flat with depressed centre

ATORN

Execution:

- With completely new special surface
- Maximum resistance against contact corrosion
- 15x greater corrosion protection against exposure to temperature, road salt and environmental influences compared to conventionally coated keys
- Up to 720 hours in the salt spray test in accordance with DIN EN ISO 9227
- Environmentally friendly chromium-VI-free coating process
- Made from chromium-vanadium steel, die-forged and hardened.
- DIN 3113 B

Advantage:

- Extremely durable and robust industrial design



Art. no.	52039 114
Brand	ATORN
Manufacturer Part Number	50066112
Tip type	Twelve-sided head
Width across flats	14 mm
Length	190 mm
Tip profile type	ENERGY profile
Jaw position	15 Degree
Surface	Special coating according to specifications
Material	Chrome-vanadium steel
DIN	3113
Gross Weight	0.086 kg
Product Group	5HB

Main EAN Code

4050293537260

