



Domestic

For refrigerators and freezers


For special features, specific benefits and areas of use see page 155



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter	Total length	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h (<2% malfunction)	Burning position	PU
						max. mm	max. mm						
4100844400	T25 10W 230-240V E14 CL	230-240	10		E14	26	57		35	1,000		n.a.	
4197444400	T25 12W 230-240V E14	230-240	12		E14	26	57		70	1,000		n.a.	
4107435600	T25 12W 125-130V E14	125-130	12		E14	26	57		70	1,000		n.a.	
4197735600	T25 15W 125-130V E14 CL REFR	125-130	15		E14	26	57		110	1,000		n.a.	
4197744400	T25 15W 230-240V E14 CL REFR	230-240	15		E14	26	57		110	1,000		n.a.	
4107744400	T25 15W 230-240V E14 CL REFR	230-240	15		E14	26	57		110	1,000		n.a.	
4199735600	T25 25W 125-130V E14 CL REFR	125-130	25		E14	26	57		172	1,000		n.a.	
4199744400	T25 25W 230-240V E14 CL REFR	230-240	25		E14	26	57		172	1,000		n.a.	



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter	Total length	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h (<2% malfunction)	Burning position	PU
						max. mm	max. mm						
41 07144400	T25 25W 230-240V E14 DB REFR	230-240	25		E14	26	57		146	1,000		n.a.	
4107244400	T25 15W 230-240V E14 DB REFR	230-240	15		E14	26	57		94	1,000		n.a.	



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter	Total length	Light centre length mm	Lumi- nous flux lm	Average life h	Individual life h (<2% malfunction)	Burning position	PU
						max. mm	max. mm						
4105135600	T25L 25W H.E. 125-130V E14 CL	125-130	25		E14	26	100		255	1,000		n.a.	
4105144400	T25L 25W H.E. 230-240V E14 CL	230-240	25		E14	26	100		217	1,000		n.a.	