

90° conical countersink HSS triple cutter with 3-edge shank

for universal use up to 1000 N/mm²

ATORN[®]



Application

For producing deep-set 90° counterbores up to 1000 N/mm².

Version

- Profile-ground extra-long triple-edge countersink

Advantage

- Radial relief ensures optimum chip breaking
- Deep-set countersinks are made easy for the user

Art. No.	11501 546
Countersink angle	90 Degree
Cutting material	HSS
Number of cutting edges	3 PCS
Surface	Uncoated
Tool holding device	HA parallel shank
Spot-facer diameter	20.5 mm
Tip diameter	3.5 mm
Length	264 mm
Shaft diameter	10 mm
f steel 700	0.16 mm/U

EAN-Code

4050293067712