



SPRING MOUNTING CLIP FOR BASIC PANEL 1ST GENERATION 4" AND LARGER NOT 4" COLOR, COMFORT PANEL 7" TO 12", TP 177 4", TP/OP 277 6", MP177, MP 277, MP377, THIN CLIENT, IPC277D 7" - 12", SHEET THICKNESS 1 TO 4 MM AMOUNT: SEE TECHNICAL DATA

### Product type designation

### Installation type/mounting

Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes

### Standards, approvals, certificates

CE mark	Yes
---------	-----

### Ambient conditions

#### Ambient temperature in operation

• Min.	0 °C
• max.	55 °C

#### Storage/transport temperature

• Min.	-20 °C
• max.	70 °C

#### Relative humidity

• Operation, max.	90 %
-------------------	------

### Mechanics/material

#### Type of housing (front)

• plastic	Yes
-----------	-----

### Dimensions

Width	20 mm
Height	35 mm
Thickness	20 mm

## Weights

Without packaging 8 g; Per unit

## Scope of supply

Delivery unit in items 20

## other

Note: TP177-4", TP/OP 277-6", MP177-6, MP277-10" T, MP277-8", MP277-8"T, MP277-10"K, MP377 12-19", TC 10", TC 15", KTP400 Basic mono, KTP600, KTP1000, KTP1500, KP700 Comfort, TP700 Comfort, KP900 Comfort, TP900 Comfort, KP1200 Comfort, TP1200 Comfort and IPC 277D 7, 9, 12"

## Usable in the following products

- Product 1 [6AV6642-0BD01-3AX0](#)
- Product 2 [6AV6643-0AA01-1AX0](#)
- Product 3 [6AV6643-0BA01-1AX0](#)
- Product 4 6AV6643-7BA00-\*
- Product 5 [6AV6642-0EA01-3AX0](#)
- Product 6 6AV6643-0D\*
- Product 7 6AV6643-0C\*
- Product 8 [6AV6643-0ED01-2AX0](#)
- Product 9 6AV6643-7CD00\*
- Product 10 6AV6643-7DD00-\*
- Product 11 6AV6644-\*
- Product 12 [6AV6647-0AA11-3AX0](#)
- Product 13 [6AV6647-0AB11-3AX0](#)
- Product 14 [6AV6647-0AC11-3AX0](#)
- Product 15 [6AV6647-0AD11-3AX0](#)
- Product 16 [6AV6647-0AE11-3AX0](#)
- Product 17 [6AV6647-0AF11-3AX0](#)
- Product 18 [6AV2124-1GC01-0AX0](#)
- Product 19 [6AV2124-0GC01-0AX0](#)
- Product 20 [6AV2124-1JC01-0AX0](#)

last modified:

12.03.2015