

## Product information

# 78 61 140

## Electronic Super Knips® XL



- Additional 15 mm longer version: greater stability, greater cutting performance
- High load capacity, made of burnished special tool steel, cutting edges additionally induction-hardened to 64 HRC
- Precision-ground cutting edges without bevel for precise and flush cutting of the finest wires, e.g. in electronics and fine mechanics
- Precisely shaped tips cut wires close to a surface from Ø 0.2 mm
- With opening spring and opening limiter for comfortable, ergonomic and fast working thanks to automatic opening and comfortable handle width
- Extremely easy movement for fatigue-free work due to precise joint with stainless steel rivet
- Special tool steel, oil hardened in multiple stages




### General

Article No.	78 61 140
EAN	4003773081685
Pliers	burnished
Head	burnished
Handles	with multi-component grips
Weight	85 g
Dimensions	140 x 83 x 14 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.4 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 2.1 mm
Jaw length (B)	12.3 mm
Jaw thickness (joint) (D)	9.2 mm
Head width (A)	15.7 mm



technical change and errors excepted



Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life