

Accessories


103-727 =
TS 35

Mounting Rail

Depending on the various applications, the mounting rails are made of steel, aluminium, or copper. All steel versions are electroplated and additionally passivated with a yellow chromate coating. For reasons of shipping, 1m mounting rails are supplied for quantities for up to 10m. Parts marked with * are available in 1 or 2m lengths.


All non-slotted mounting rails can be provided with fixing holes (please state dimensions b and l₂). Additionally, all non-slotted steel rails can be supplied with welded steel bolts (please state dimensions a and the desired bolt).

TS35 x 7.5
Steel, Slotted Steel or Aluminium




Fixing holes
Dimension b to specs.
(dia. 3.5/4.5/5.5/7)
Dimension l₂ to specs.
Dimension l₁ to 2 m

TS35 x 15
Steel or Slotted Steel



Fixing holes
for TS35 x 15, steel
Dimension b to specs.
(dia. 3.5/4.5/5.5/7)
Dimension l₂ to specs.
Dimension l₁ to 3 m

TS35 x 15/2.3
Steel or Copper



Fixing holes
Dimension b to specs.
(dia. 3.5/4.5/5.5/7)
Dimension l₂ to specs.
Dimension l₁ to 3 m

Technical Data

Material
Standard
Short-circuit resistance
Max allowable rated current PEN function

Ordering Data

Steel, l = 2m
Steel, l = 1m
Slotted steel, l = 2m
Slotted steel, l = 1m
Alu
Slotted Alu
Cu
PVC grey

End bracket

EW35	50	038356
------	----	--------

For TS32 slotted rail

Mounting rail support

(M5 Thread)	TSTW 5	10	017810
(M6 Thread)	TSTW 6	10	016400
(M6 Thread)	TST 2	10	010170

Fixing screw

Fixing screw with hexagon socket for	FKSC M 6x12	50	035350
TSTW and TST	FKSC M 6x8	50	064260
	FKSC M 5x8	50	029590

Mounting base

Steel with M4 thread	FM 4	40	068790
PA 66 Orange	Mounting base	20	064626
With M3 and M5 thread (cream)			
With M6 and M4 thread (grey)			
or with M5 and M3 (black)			
Support Block	SH 2	10	049492

Steel	Aluminium
St 2 plated	AL bare
DIN EN 50022	DIN EN 50022
16Ω	35Ω

Type	Qty.	Cat. No.
TS35 x 7.5	1.0m	038340
TS35 x 7.5	1.0m	038341
TS35 x 7.5	1.0m	051450
TS35 x 7.5	1.0m	051451
TS35 x 7.5	1.0m	033080

Type	Qty.	Cat. No.
EW35	50	038356

Type	Qty.	Cat. No.
TSTW 5	10	017810
TSTW 6	10	016400
TST 2	10	010170

Type	Qty.	Cat. No.
FKSC M 6x12	50	035350
FKSC M 6x8	50	064260
FKSC M 5x8	50	029590

Type	Qty.	Cat. No.
FM 4	40	068790
Mounting base	20	064626
SH 2	10	049492

Steel
St 2 plated
25Ω

Type	Qty.	Cat. No.
TS35 x 15	1.0m	023640
TS35 x 15	1.0m	023641
TS35 x 15	1.0m	023650
TS35 x 15	1.0m	023651

Type	Qty.	Cat. No.
EW35	50	038356

Type	Qty.	Cat. No.
TSTW 5	10	017810

Type	Qty.	Cat. No.
FKSC M 6x12	50	035350
FKSC M 6x8	50	064260
FKSC M 5x8	50	029590

Type	Qty.	Cat. No.
FM 4	40	068790
Mounting base	20	064626
SH 2	10	049492

Steel	Copper
St 2 plated	Cu bare
DIN EN 50022	
50Ω	150Ω
	335A

Type	Qty.	Cat.
TS35 x 15/2.3	1.0m	04
TS35 x 15/2.3	1.0m	04
TS35 x 15/2.3	1.0m*	02

Type	Qty.	Cat.
EW35	50	03

Type	Qty.	Cat.
TSTW 5	10	01
TSTW 6	10	01
TST 2	10	01

Type	Qty.	Cat.
FKSC M 6x12	50	03
FKSC M 6x8	50	06
FKSC M 5x8	50	02

Type	Qty.	Cat.
FM 4	40	06
SH 2	10	04