

Product information

87 41 250

Multiple Slip Joint Spanner



- For metric and imperial nuts and screws with widths across flats from 10 to 32 mm (3/8" up to 1 1/4"); self-locking from 17 mm: no slipping on the workpiece
- Zero-backlash gripping of metric or imperial hexagonal headed screws, no rounding of bolt heads
- Reliable and tight gripping of rounded, rusty, or thick coated bolts and screws
- Ideal for work on vehicle brake systems
- Quick tightening of bolted connections using ratchet action
- Push the button for adjustment on the workpiece, also possible with one hand only
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Favourable lever action: optimum transmission of force
- Pinch guard prevents operators' fingers being pinched
- Replaces a set of wrenches, ideal for tightening locknuts
- Chrome vanadium electric steel, forged, multi stage oil-hardened




General

Article No.	87 41 250
EAN	4003773054566
Pliers	grey atramentized
Head	polished
Handles	with non-slip plastic coating
Weight	328 g
Dimensions	250 x 48 x 13 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Adjustment positions	15
Capacities for nuts	Ø 3/8 – 1 1/4 Inch
Capacities for nuts	Ø 10 – 32 mm

technical change and errors excepted



Self-locking: no slip on workpieces; less effort required



In operation on rusted nut with rounded edges



Fine adjustment by pushing a button: fast and comfortable.