

## Drawer cabinets

Mobile with a pair of roller carriers and nylon rollers Ø 100 mm

### Application:

For day-to-day heavy-duty use in workshops

### Version:

- All drawers with full extension
- Individual drawer lock as standard feature to prevent the cabinet from tipping over
- Perforated, slotted drawers provide a secure hold
- Very robust construction for a wide variety of applications and very demanding requirements

### Advantage:

- Optimum wall height to keep items from falling out and getting lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to the lack of crossbars on the differential extension slide
- Full extension - clear view and optimal access

### Delivery:

1 anti-roll-off edging, 4-sided, 1 sliding rod, 1 roller carrier pair with nylon rollers, Ø 100 mm



<b>Art. no.</b>	<b>50300 820</b>
<b>Number of drawers</b>	5 PCS
<b>Height</b>	890 mm
<b>Width</b>	411 mm
<b>Depth</b>	725 mm
<b>Height x width x depth</b>	890 x 411 x 725 mm
<b>Housing height</b>	700 mm
<b>Draw width (inner dimension) x drawer depth (inner dimension)</b>	300 x 600 mm
<b>Load-carrying capacity per drawer</b>	75 kg
<b>Drawer lock</b>	Single lock right
<b>Drawer front height</b>	2 x 75 mm, 3 x 150 mm
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Light grey RAL 7035
<b>Cabinet equipment</b>	Pair of castors
<b>With sliding handle</b>	Yes
<b>Height of roller carrier pair</b>	137 mm
<b>Wheel diameter</b>	100 mm
<b>Material of wheel</b>	Nylon (polyamide)
<b>Information about the direction</b>	Along
<b>Load-carrying capacity of roller</b>	400 kg
<b>Opening/closing system</b>	Key Lock
<b>Rim height</b>	53 mm
<b>Clear height</b>	600 mm
<b>LISTA unit</b>	18 x 36 E

### EAN-Code

7612269077285