

Angular milling cutter 90°

For indexable milling insert WNEX 0806..

ATORN®

Application

Powerful angular milling cutter with particularly economic, double-sided indexable insert with 6 cutting edges. Flexible use for multiple machining steps, such as face, angular, trim and groove milling.

Version

- Wear-resistant, nickel-plated version
- With internal cooling

Advantage

- 6 cutting edges on double-sided indexable insert
- Special chip shape geometry for low power consumption
- Large plate thickness for optimum process reliability
- Optimised plane cutting edge for high surface quality



Art. No.	16020 500
Cutting edge diameter	100 mm
Length	50 mm
Bore diameter	32 mm
max. ap	6 mm
Number of cutting edges	8 PCS

EAN-Code

4050293540017