


# Beacon LED Projector - Gobo

Beacon LED Gobo Projector O/B 4000K Three Circuit Track - White  
2055946

## Product features



- Beacon Projector offers precision light exactly where it is needed. The Gobo Projector with the use of ROSCO filters allow you to project a still image printed/cut/lasered onto a specially made glass/metal/acetate filter - for example a company logo, text, shapes, images. High colour rendering CRI 97 typical. IR/UV free light source without heat radiation. LED technology provides an energy efficient solution with reduced maintenance costs.




## PRODUCT OVERVIEW

Product name	Beacon LED Gobo Projector O/B 4000K Three Circuit Track - White
Technology	LED
Housing	Aluminium
Mount	Track mounting
Fixture rating	Enclosed
General application	Hospitality, Museums & Galleries
ETIM Class	EC001744
E-number FI	4260880
Warranty	5 years
Fixture luminous flux (lm)	474
Luminaire efficacy (lm/W)	14
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	97
Colour Variation Initial (SDCM)	SDCM3
Photobiological Risk Group	RG1
Total power consumption (W)	35
Product Voltage (V)	240
Electrical protection	Class II
Control gear type	Electronic ballast
Control gear mounting	Integral
Dimmable	Yes
Dimming method	1-10V (Analogue)
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK02
Product EAN number	5025768559466

## PHOTOMETRY

## Beacon LED Projector - Gobo

*Beacon LED Gobo Projector O/B 4000K Three Circuit Track - White*  
**2055946**



## TECHNICAL DRAWINGS

