



## FGxx



### SCHUTZGITTER



FG25



FGxxx

Metallgitter für Standard-Lüfter 25x25mm bis Ø150/172 bzw. Ø172mm. Material: Stahldraht, verchromt.

Art. Nr.	Typ	Lüftergröße [mm]	Bohrungsabstände und -durchmesser D / d [mm]	Höhe [mm]	Anzahl Ringe	VPE [Stk.]
912510000	FG25 Metallgitter	25x25	28.2 / 3.3	5	2	100
913010000	FG30 Metallgitter	30x30	24 / 3.2	4.8	2	100
914010000	FG40 Metallgitter	40x40	32 / 4.0	4.8	2	100
915010000	FG50 Metallgitter	50x50	42 / 4.0	5.0	3	100
915010001	FG50-40 Metallgitter	50x50	40 / 4.0	5.0	3	100
916010000	FG60 Metallgitter	60x60	50 / 4.6	5.0	4	100
918010000	FG80 Metallgitter	80x80	71.5 / 4.9	5.5	5	100
919210000	FG92 Metallgitter	92x92	82.5 / 4.9	5.5	6	100
911210000	FG120 Metallgitter	120x120	105 / 4.9	5.5	8	100
912710000	FG127 Metallgitter	127x127	113.3 / 4.6	6.0	8	100
915110000	FG150 Metallgitter	172/150	162 / 4.8	6.5	9/10	100
917210000	FG172 Metallgitter	Ø172	162 / 4.8	6.5	10	100



Schutzgitter aus hochwertigem Kunststoff IP20 für Standard Lüfter von 40x40 mm bis 120x120 mm bzw. Ø150.

Art. Nr.	Typ	Lüfter Größe [mm]	Maße LxBxH [mm]	Verpackung [Stk.]
914020000	FG40K Schutzgitter, IP20	40x40	42.3x42.3x3.3	100
916020000	FG60K Schutzgitter, IP20	60x60	60x60x6.0	100
918020000	FG80K Schutzgitter, IP20	80x80	81x81x5.5	100
919220000	FG92K Schutzgitter, IP20	92x92	92x92x5.5	100
911220000	FG120K Schutzgitter, IP20	120x120	121x121x6.5	100
911220000	FG150K Schutzgitter, IP20	Ø150, 150/172	153x173x10.8	50