

Lockwashers DIN 5406 for Locknuts DIN 981

Material: Steel.


Steel, zinc-plated.

Stainless steel 1.4301 (AISI 304).

Strength min. 350 N/mm².

Safety plates for locknuts DIN 981.

A keyway is required on the shaft thread.



Ordering Details: e.g.: Product No. 65363001, Lockwasher DIN 5406 MB 0

Product No. Steel	Product No. Zinc-plated	Product No. Stainless	Type	matching nut type	d ₁ mm	d ₂ mm	d ₃ mm	e mm	f mm	b ₁ mm	s mm	Weight g
653 630 01	653 630 81	653 995 30	MB 0	KM 0	10	21	13,5	3	8,5	3	1	1
653 632 01	653 632 81	653 995 32	MB 1	KM 1	12	25	17	3	10,5	3	1	2
653 634 01	653 634 81	653 995 34	MB 2	KM 2	15	28	21	4	13,5	4	1	3
653 637 01	653 637 81	653 995 37	MB 3	KM 3	17	32	24	4	15,5	4	1	3
653 640 01	653 640 81	653 995 40	MB 4	KM 4	20	36	26	4	18,5	4	1	4
653 644 01	653 644 81	653 995 44	MB 5	KM 5	25	42	32	5	23	5	1,25	6
653 648 01	653 648 81	653 995 48	MB 6	KM 6	30	49	38	5	27,5	5	1,25	8
653 653 01	653 653 81	653 995 53	MB 7	KM 7	35	57	44	6	32,5	5	1,25	10
653 658 01	653 658 81	653 995 58	MB 8	KM 8	40	62	50	6	37,5	6	1,25	12
653 662 01	653 662 81	653 995 62	MB 9	KM 9	45	69	56	6	42,5	6	1,25	15
653 665 01	653 665 81	653 995 65	MB 10	KM 10	50	74	61	6	47,5	6	1,25	16
653 668 01	653 668 81	653 995 68	MB 11	KM 11	55	81	67	8	52,5	7	1,5	20
653 671 01	653 671 81	653 995 71	MB 12	KM 12	60	86	73	8	57,5	7	1,5	25
653 673 01	653 673 81	653 995 73	MB 13	KM 13	65	92	79	8	62,5	7	1,5	29
653 675 01	653 675 81	653 995 75	MB 14	KM 14	70	98	85	8	66,5	8	1,5	33
653 678 01	653 678 81	653 995 78	MB 15	KM 15	75	104	90	8	71,5	8	1,5	36
653 680 01	653 680 81	653 995 80	MB 16	KM 16	80	112	95	10	76,5	8	1,8	46
653 683 01	653 683 81	653 995 83	MB 17	KM 17	85	119	102	10	81,5	8	1,8	52
653 685 01	653 685 81	653 995 85	MB 18	KM 18	90	126	108	10	86,5	10	1,8	62
653 687 01	653 687 81	653 995 87	MB 19	KM 19	95	133	113	10	91,5	10	1,8	67
653 690 01	653 690 81	653 995 90	MB 20	KM 20	100	142	120	12	96,5	10	1,8	77
653 638 01	653 638 81	-	MB 21	KM 21	105	145	126	12	100,5	12	1,8	83
653 639 01	653 639 81	-	MB 22	KM 22	110	154	133	12	105,5	12	1,8	94
653 641 01	653 641 81	-	MB 23	KM 23	115	159	137	12	110,5	12	2,0	108
653 642 01	653 642 81	-	MB 24	KM 24	120	164	138	14	115	12	2,0	105
653 643 01	653 643 81	-	MB 25	KM 25	125	170	148	14	120	12	2,0	118
653 645 01	653 645 81	-	MB 26	KM 26	130	175	149	14	125	12	2,0	113
653 646 01	653 646 81	-	MB 27	KM 27	135	185	160	14	130	14	2,0	144
653 647 01	653 647 81	-	MB 28	KM 28	140	192	160	16	135	14	2,0	142
653 649 01	653 649 81	-	MB 29	KM 29	145	202	171	16	140	14	2,0	168
653 650 01	653 650 81	-	MB 30	KM 30	150	205	171	16	145	14	2,0	155
653 651 01	653 651 81	-	MB 31	KM 31	155	212	182	16	147,5	16	2,5	209
653 652 01	653 652 81	-	MB 32	KM 32	160	217	182	18	154	16	2,5	229
653 654 01	653 654 81	-	MB 33	KM 33	165	222	193	18	157,5	16	2,5	241
653 655 01	653 655 81	-	MB 34	KM 34	170	232	193	18	164	16	2,5	247
653 656 01	653 656 81	-	MB 36	KM 36	180	242	203	20	174	18	2,5	268
653 657 01	653 657 81	-	MB 38	KM 38	190	252	214	20	184	18	2,5	278
653 659 01	653 659 81	-	MB 40	KM 40	200	262	226	20	194	18	2,5	293