

Product information

49 21 A31

Precision Circlip Pliers

For external circlips on shafts

DIN 5254 B



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Large contact faces on the tips: no distortion of circlips, easy fitting
- Bolted joint: precise, zero backlash operation of pliers
- Internal opening spring, protected and captive
- Non-slip plastic coating on the handles
- Angled tips
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

MM \varnothing $\angle 90^\circ$



General

Article No.	49 21 A31
EAN	4003773048848
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	272 g
Dimensions	210 x 42 x 14 mm
Standard	DIN 5254 B
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Size of shaft	\varnothing 40 – 100 mm
Tips (diameter)	2.3 mm

technical change and errors excepted



Spring inside the joint: the spring is protected inside the precisely bolted joint. It does not hinder work and cannot get dirty or lost.