

9013TT pneumatic impact screwdriver

Square drive 3/4 inch



Application:

Compact design – optimised for working in confined spaces

Execution:

- Exhaust air discharged downwards through the handle
- Detachable handstrap – adjustable by 360°
- 2 power levels in clockwise rotation, 1 power level in anti-clockwise rotation
- Cold-insulating handle

Delivery:

Includes Hand grip and coupling plug



Art. no.	75065 048
Brand	HAZET
Manufacturer Part Number	9013TT
Model	9013TT
Suitable for screw	M32
Max. tightening torque	2170 Nm
Max. releasing torque	4100 Nm
Max. idle speed	5200 rpm
Air consumption	244 l/min
Tool holding device	3/4-inch external square
Hammer mechanism system	Twin hammer mechanism
Length	213 mm
Connection thread	IT 3/8 inch
Inner hose diameter	13 mm
Operating pressure	6.3 bar
Sound-pressure level	99.5
Weight	4.5 kg
With right/left-hand rotation	Yes
Gross Weight	5.580 kg
Product Group	738

EAN

4000896227143