

## Boring bar AMI right

For internal recessing and copy turning using AD and AE cutting inserts

**ATORN**

### Application:

For recessing and copy turning, internal

### Execution:

- Precision-manufactured steel support, nickel-plated and hardened with clamping element



|                                   |                  |
|-----------------------------------|------------------|
| <b>Art. no.</b>                   | <b>17673 770</b> |
| <b>Brand</b>                      | ATORN            |
| <b>Manufacturer Part Number</b>   | 12371010         |
| <b>Suitable for knife width</b>   | 3 mm             |
| <b>Shank diameter</b>             | 25 mm            |
| <b>Plunge depth</b>               | 9 mm             |
| <b>Length</b>                     | 200 mm           |
| <b>Immersion depth</b>            | 9 mm             |
| <b>Clamping surface height</b>    | 24.5 mm          |
| <b>Adjustment rate via centre</b> | 22 mm            |
| <b>Min. bore diameter</b>         | 31.1 mm          |
| <b>Tool design</b>                | Right            |
| <b>Gross Weight</b>               | 0.670 kg         |
| <b>Product Group</b>              | 1FF              |

### EAN

4050293740349

