

Product information

83 60 010

Pipe Wrench S-Type

With fast adjustment

DIN 5234

- Pinch guard prevents operators' fingers being pinched
- Time-saving, precise adjustment of the gripping width directly on the workpiece at the push of a button
- Less effort required due to self-locking action
- No unintentional shifting of the pliers handles
- High wear resistance due to the additionally hardened teeth
- Maximum load capability thanks to completely hardened handles
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	83 60 010
EAN	4003773075424
Pliers	red powder-coated
Weight	955 g
Dimensions	330 x 70 x 25 mm
Standard	DIN 5234
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Capacities for pipes (diameter)	Ø 1 5/8 Inch
Capacities for pipes (diameter)	Ø 42 mm
Capacities for nuts	42 mm
Inner diameter, inches	Ø 1 Inch
Pipe inner dia.	25 mm

technical change and errors excepted



